

BZGY908 COLOUR ASSESSMENT CABINETS





MODEL NO.

BZGY908 Series

Applications

Be a universal preferred choice for fastness, closer and accuracy color matching of textiles, dyeing and garment industry.

Related Standards

STANDARDS	AATCC, ISO etc.
------------------	-----------------

Features

- Use Philips™ and GE™ lamps, Philips™ bulb (F light source), life-time of each lamp up to 4000h (recommended max operation time: 2000h for more accurate test result).
- Use Ramtron™ memory, with individual lighting lifetime record function and operating times record function (by on/off) (see figures in page above).
- Manually sequence lighting function, Operators can make any combination from existing lights by easily press corresponding button of lights.
- With energy-save function, auto power off when reach 2 hours without any operation.
- Optional 45° fixed angel specimen stand, make assessment process more comfortable and comparable.
- Available light source
- MACBETH or VERIVIDE lamp can be provided.

Source	Kelvin/wavelength	Lamp type	Supplier	Use
D65	6500K	Fluorescent Artificial daylight	PHILIPS™ Or MACBETH or VERIVIDE	International standard artificial daylight
TL84	4000K	Fluorescent Triphosphor lamp	PHILIPS™ Or VERIVIDE	European and Japanese shop light source
CWF	4150K	Fluorescent	GE™	US shop light source



FANYUAN INSTRUMENT (HF) CO., LTD.
DOWELL SCIENCE AND TECHNOLOGY (HK) CO., LTD.
 ADD: Tianyuan Road 9#, High-tech Zone, Hefei City, China Postal Code: 230088
 TEL: +86-551-65232508
 FAX: +86-551-65232507
 Email: sales@hkdownell.com
 Website: <http://www.fyichina.com.cn>

		Cool write		
F/A	2700K	Incandescent Filament light	PHILIPS™	Yellow light source
UV	Wavelength 365nm	Fluorescent Black light	GE™	Ultraviolet lamp
TL83	3000K	Fluorescent	PHILIPS™	Other US shop light source
U30	3000K	Fluorescent	PHILIPS™	Other US shop light source

Key Specification:

Model	BZGY908A	BZGY908B	BZGY908C	BZGY908D	BZGY908E	BZGY908F
Light types	6	4	5	6	7	8
Light source and power	D65(18W) UV(18W) TL84(18W) F (40W) CWF(18W) TL83(18W)	D65(18W) UV(18W) TL84(18W) F (40W)	D65(18W) UV(18W) TL84(18W) F (40W) CWF(18W)	D65(36W) UV(40W) TL84(36W) F (40W) CWF(40W) TL83(36W)	D65(18W) UV(18W) TL84(18W) F (40W) A(60W) CWF(18W) TL83(18W)	D65(18W) UV(18W) TL84(18W) F (40W) A(60W) CWF(18W) TL83(18W) U30(20W)
Cavity (mm)	710×530×570	710×405×570	710×405×570	1310×600×800	710×630×570	710×730×570
Power supply	AC220V, 50Hz					
weight	35Kg	28Kg	28KG	60Kg	40KG	45KG

Standard configuration:

Model	BZGY908A	BZGY908B	BZGY908C	BZGY908D	BZGY908E	BZGY908F
Main machine	1set	1set	1set	1set	1set	1set
D65 lamp (18W)	2pcs	2pcs	2pc		2pcs	2pcs



FANYUAN INSTRUMENT (HF) CO., LTD.
DOWELL SCIENCE AND TECHNOLOGY (HK) CO., LTD.
 ADD: Tianyuan Road 9#, High-tech Zone, Hefei City, China Postal Code: 230088
 TEL: +86-551-65232508
 FAX: +86-551-65232507
 Email: sales@hkdownell.com
 Website: <http://www.fyichina.com.cn>

D65 lamp (36W)				2pcs		
UV lamp(18W)	1pc	1pc	1pc		1pc	1pc
UV lamp(40W)				1pc		
F Bulb(40W)	4pcs	4pcs	4pcs	6pcs	4pcs	4pcs
A Bulb(60W)					2pcs	2pcs
CWF lamp(18W)	2pcs		2pcs		2pcs	2pcs
CWF lamp(40W)				2pcs		
TL83 lamp(18W)	2pcs				2pcs	2pcs
TL83 lamp(36W)				2pcs		
U30 Lamp(20W)						2pcs
TL84 lamp(18W)	2pcs	2pcs	2pcs		2pcs	2pcs
TL84 lamp(36W)				2pcs		

Optional Accessories:

No.	Item
1	45°Fixed angel specimen stand
2	Other customized brands lamps