




WWW.FYICHINA.COM.CN

WENZHOU FANGYUAN INSTRUMENT CO., LTD.
DOWELL SCIENCE AND TECHNOLOGY (HONGKONG) CO., LTD.
ADD: ROOM 1401 CAMBRIDGE HOUSE, 26-28 CAMERON ROAD,
TSIMSHATSUI, KL, HONGKONG
TEL: +86-755-83638931
Fax: +86-755-26747651

LAB KNITTER





WWW.FYICHINA.COM.CN

WENZHOU FANGYUAN INSTRUMENT CO., LTD.
DOWELL SCIENCE AND TECHNOLOGY (HONGKONG) CO., LTD.
ADD: ROOM 1401 CAMBRIDGE HOUSE, 26-28 CAMERON ROAD,
TSIMSHATSUI, KL, HONGKONG
TEL: +86-755-83638931
Fax: +86-755-26747651

MODEL NO.

HS808M-6F

Application:

This machine has been designed with a number of unique features that makes it a user-friendly and economical machine for operators with low knowledge on knitting machine.

It is for the production of tubular knitted fabric, for yarn uniformity assessment, dyeing affinity quality control of yarn.

Related Standards:



Features:

- Equipped with single cylinder 3,3/4” in diameter, selectable number of needles and fineness;
- Fitted with stepper motor to control yarn tension and position
- Auto oiling system for cylinder
- Use MCU and control panel to directly set stitch density, speed, no. of loop, production, etc.
- Special regulation mechanism for yarn feeding speed
- LED display to show machine functions

Key Specification:

- Needle Cylinder: 3+3/4” in diameter
- Speed 250-300RPM
- Power supply 380V,50HZ, 2500W
- Range of available interchangeable cylinders

CODE	No. of Needles	Needle Gauge	Count of Yarn(Dtex)
808M-108	108	24	400-2000
808M-120	120	24	300-1500
808M-132	132	36	200-1500
808M-144	144	36	200-1000
808M-200	200	48	100-400
808M-220	220	60	70-300



WWW.FYICHINA.COM.CN

WENZHOU FANGYUAN INSTRUMENT CO., LTD.
DOWELL SCIENCE AND TECHNOLOGY (HONGKONG) CO., LTD.
ADD: ROOM 1401 CAMBRIDGE HOUSE, 26-28 CAMERON ROAD,
TSIMSHATSUI, KL, HONGKONG
TEL: +86-755-83638931
Fax: +86-755-26747651

- Cop Changing System: 24 positions
- Air supply: 0.6MPa
- Size: 100×95×170cm (L×M×H)
- Weight: 300Kg

Standard configuration:

No.	Item	Quantity
1	Main machine	1 set
2	Cop Changing System(24 position)	1 set
3	Cylinder(808M-108,120,132,144,200,220)	Specify one pcs